



● HOTMELT - PILLOW

ÜRÜN	AMBALAJ TÜRÜ	VİSKOZİTE	YUMUŞAMA NOKTASI	RENK	UYGULAMA ALANLARI
HM-090	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	2000 mPas ± 500	80 ± 5 °C	TRANSPARAN BEYAZ	YATAK & KADIN BAKIM ÜRÜNLERİ
HM-140	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	2000 mPas ± 500	95 ± 5 °C	TRANSPARAN BEYAZ	MASKELEME BANTİ
HMP-500	KUTU : ~ 8 KG PILLOW : ~ 40 ± 3 GR	3500 mPas ± 500	110 ± 10 °C	TRANSPARAN BEYAZ	PAKET YAY