



Yüksek kaliteli Hotmelt yapıştırıcıları, başta mobilya, yatak, ambalaj ve otomotiv sektörü olmak üzere birçok endüstriyel uygulamada hızlı, güçlü ve verimli çözümler sunar.

Hotmelt yapıştırıcılar, ısıtılarak uygulanır ve soğuduklarında hızla güçlü bir yapışma sağlar. Solvent veya su içermezler; bu sayede çevre dostudur ve üretim süreçlerinde enerji ve zaman tasarrufu sağlar.

High- quality hotmelt adhesives provide fast, strong, and efficient solutions for many industrial applications, especially in the furniture, mattress, packaging, and automotive sectors.-

Hotmelt adhesives are applied by heating and quickly form a strong bond as they cold. They do not contain solvents or water, making them environmentally friendly and enabling energy and time savings in production processes.



● HOTMELT - PILLOW

ÜRÜN	AMBALAJ TÜRÜ	VİSKOZİTE	YUMUŞAMA NOKTASI	RENK	UYGULAMA ALANLARI
HM-030	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	1500 mPas ± 500	85 ± 5 °C	TRANSPARAN SARI	YATAK
HM-056	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	3000 mPas ± 500	80 ± 5 °C	TRANSPARAN SARI	YATAK
HM-080	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	2000 mPas ± 500	80 ± 5 °C	TRANSPARAN SARI	YATAK
HM-080 B	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	2000 mPas ± 500	85 ± 5 °C	TRANSPARAN SARI	YATAK
HM-092	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	2000 mPas ± 500	90 ± 5 °C	TRANSPARAN SARI	ÇUVAL
HM-095	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	2000 mPas ± 500	85 ± 5 °C	TRANSPARAN SARI	YATAK
HM-095 B	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	4000 mPas ± 500	85 ± 5 °C	TRANSPARAN SARI	YATAK
HM-098	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	1250 mPas ± 300	85 ± 5 °C	TRANSPARAN SARI	TEKSTİL BACK SHEET & MEDİKAL LAMİNASYON VE BEBEK BEZİ YAPILANDIRMASI
HM-120	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	850 mPas ± 200	75 ± 5 °C	TRANSPARAN SARI	TEKSTİL LAMİNASYONU , ETİKETLEME & DÖŞEME
HM-150	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	2000 mPas ± 500	95 ± 5 °C	TRANSPARAN SARI	BEBEK BEZİ LASTİK APRESİ
HM-2012	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	8000 mPas ± 1000	95 ± 5 °C	TRANSPARAN SARI	ETİKETLEME & FATURA CÜZDANI
HM-2015	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	12000 mPas ± 1500	90 ± 5 °C	TRANSPARAN SARI	MEDİKAL BANTLAR

HM-2016	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	12500 mPas ± 1500	105 ± 5 °C	TRANSPARAN SARI	BANT
HM-2046	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	5000 mPas ± 1000	75 ± 5 °C	TRANSPARAN SARI	KARGO POŞETİ
HM-2049	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	5000 mPas ± 1000	85 ± 5 °C	TRANSPARAN SARI	ISLAK MENDİL KAPAĞI
HM-2049 LV	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	2000 mPas ± 1000	85 ± 5 °C	TRANSPARAN SARI	ISLAK MENDİL KAPAĞI
HMP-180	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	2000 mPas ± 500	95 ± 5 °C	TRANSPARAN SARI	YATAK
HMP-250	KUTU : ~10 KG PILLOW : ~ 40 ± 3 GR	4000 mPas ± 500	100 ± 10 °C	TRANSPARAN SARI	YATAK